

# MC-R SERIES

## ROTARY CAPPING MACHINE



The MC-R series cappers can handle these kind of containers:



Range of closures applicable by MC-R cappers include: **aluminum caps, pilfer-proof caps, screw-caps, press-on caps** and **plastic pumps**.

### MC-R1 AND MC-R2 HIGHLIGHTS

- Screw-cap torqueing can come with **magnetic** or **pneumatically** operated clutch.
- **Pilfer-proof sealing** is achieved with traditional style spinning head.
- Sealing of pharmaceutical aluminum cap for injectables with **rolling discs** or **spinning head with pressure control**.
- Possibility to **reject vial without rubber stopper** or **misaligned stopper** at infeed, prior to capping operations.
- **In line process** (100 % torque control).
- **Small footprint**.

### MC-R12 HIGHLIGHTS

- MC-R12 for plug insertion **perform this operation by vacuum**.
- Screw-cap torqueing can come with **magnetic** or **pneumatically** operated clutch.
- **Pilfer-proof sealing** is achieved with traditional style spinning head.
- Sealing of pharmaceutical aluminum cap for injectables with **blade** or **spinning head**.
- Possibility to **reject vial without rubber stopper** or **misaligned stopper** at infeed, prior to capping operations.
- **Small footprint**.

#### TECHNICAL DATA

#### DEVELOPMENT

#### MOVEMENT

#### OUTPUT

#### CONTAINMENT

#### MC-R1 Single Pitch

Rotary

Intermittent

Up to 50 pcs/min

o-RABS c-RABS Isolator

#### MC-R2 Double Pitch

Rotary

Intermittent

Up to 100 pcs/min

o-RABS c-RABS Isolator

#### MC-R12

Rotary

Continuous

Up to 600 pcs/min

o-RABS c-RABS Isolator